

SILENTA[®]



Spirex
Safety technologies

www.spirex.es

PROTECCIÓN AUDITIVA

SILENTA GROUP OY, DESDE 1962 FABRICANDO Y DESARROLLANDO PROTECTORES AUDITIVOS PARA NECESIDADES INDUSTRIALES, MILITARES Y DE TIEMPO LIBRE.

SILENTA[®]

HEARING PROTECTOR TECHNOLOGY



SILENTA[®]

HEARING PROTECTOR TECHNOLOGY

WE HAVE SPECIALIZED IN THE DEVELOPMENT AND
PRODUCTION OF HIGH QUALITY HEARING PROTECTORS
FOR OVER 50 YEARS



Supermax black



Ergomax grey



Splendor High Visibility green



Aurora LT red



Silenta KID fluorescent pink



MIL II Nato Green

SILENTA®

HEADBAND MOUNTED

Foldable headband with comfortable pressure

Sales carton 80x54x39 cm pc / kg

SUPERIOR NOISE ATTENUATION SNR 33 - 36

	P/N	SNR	Added value	Box/bag	
Supermax black	9900000	36	Supreme user comfort	box	60 pcs / 19,0 kg
Supermax red	9901000	36		box	60 pcs / 19,0 kg
Supermax blue	9902100	36		box	60 pcs / 19,0 kg
Supermax High Visibility	9906600	36		box	60 pcs / 19,0 kg
Hygiene Kit Supermax	6001000				
Ergomax black	9800000	33	Dielectric, prize-winning design	box	50 pcs / 18,0 kg
Ergomax burgundy	9801100	33		box	50 pcs / 18,0 kg
Ergomax grey	9804000	33		box	50 pcs / 18,0 kg
Hygiene Kit Ergomax	6000800				

HIGH NOISE ATTENUATION SNR 31 - 32

Aurora black	5800000	31	classic designs	box	60 pcs / 22,0 kg
Splendor black	8900000	32		box	60 pcs / 18,0 kg
Splendor red	8901000	32		box	60 pcs / 18,0 kg
Splendor High Visibility	8906600	32		box	60 pcs / 18,0 kg
Hygiene Kit Aurora & Splendor	6000800				
Aurora LT black	5700000	31	Dielectric, 360° rotating headband	bag	75 pcs/ 19,5 kg
Aurora LT red	5701000	31		bag	75 pcs/ 19,5 kg
Hygiene Kit Aurora LT	6000300				

MEDIUM NOISE ATTENUATION SNR 27 - 28

Auroramil black	5600000	27	high visibility headband	box	60 pcs / 20,0 kg
Splendormil black	8600000	27		box	60 pcs / 18,0 kg
Splendormil High Visibility	8606600	27		box	60 pcs / 18,0 kg
Silenta KID High Visibility green	7905300	27		box	60 pcs / 18,0 kg
Silenta KID High Visibility pink	7901300	27		box	60 pcs / 18,0 kg
Silenta KID blue	7902100	27		box	60 pcs / 18,0 kg
Silenta KID red	7901000	27		box	60 pcs / 18,0 kg
Hygiene Kit	6000300				
MIL II Nato Green	7705000	28	for shooting	box	60 pcs / 18,0 kg
MIL II Black	7700000	28		box	60 pcs / 18,0 kg
Hygiene Kit MIL II	6006000				

LOW NOISE ATTENUATION SNR 21

Bel II red	8401000	21		bag	90 pcs/17 kg
------------	---------	----	--	-----	--------------



HELMET MOUNTED

Silenta helmet mounting arm and Clip-On adapter system enables attachment to most helmets on the market

Sales carton
80x54x39 cm
pc / kg

	P/N	SNR	Added value	Box/bag	
SUPERIOR NOISE ATTENUATION SNR 32 - 35					
Supermax Cap black	9960000	35	Easy working / parking position	box	60 pcs / 22,0 kg
Supermax Cap red	9961000	35		box	60 pcs / 22,0 kg
Supermax Cap blue	9962100	35		box	60 pcs / 22,0 kg
Supermax Cap High Visibility	9966600	35		box	60 pcs / 22,0 kg
Ergomax Cap black	9810000	32	Dielectric ABS plastic	box	60 pcs / 21,0 kg
Ergomax Cap burgundy	9811100	32		box	60 pcs / 21,0 kg
Ergomax Cap grey	9814000	32		box	60 pcs / 21,0 kg



Supermax Cap red



Ergomax Cap burgundy

HIGH NOISE ATTENUATION SNR 31					
Aurora Cap black	5860000	31	classic designs	box	60 pcs / 23,0 kg
Splendor Cap black	8960000	31		box	60 pcs / 20,0 kg
Splendor Cap HV	8966600	31		box	60 pcs / 20,0 kg



Aurora Cap black

MEDIUM NOISE ATTENUATION SNR 29					
Auroramil Cap black	5610000	29	classic designs	box	60 pcs / 19,5 kg
Splendormil Cap black	8610000	29		box	60 pcs / 19,5 kg
Splendormil Cap red	8611000	29		box	60 pcs / 19,5 kg
Splendormil Cap High Visibility	8616600	29		box	60 pcs / 19,5 kg



Auroramil Cap black



NECKBAND MODELS

To be worn with other head protection and whenever the headband models are not proper

Sales carton
80x54x39 cm
pc / kg

	P/N	SNR	Added value	Box/bag	
Aurora NB black	5830000			box	60 pcs / 20,0 kg
Splendor NB black	8930000			box	60 pcs / 18,0 kg
Splendor NB High Visibility	8936600			box	60 pcs / 18,0 kg
Auroramil NB black	5630000			box	60 pcs / 18,0 kg
Splendormil NB black	8630000			box	60 pcs / 18,0 kg
Splendormil NB High Visibility	8636600			box	60 pcs / 18,0 kg



Splendor NB black



Splendormil NB black

MAINTENANCE

Cushions may deteriorate with use and should be examined at frequent intervals for cracking and leakage. For example, inflexible, worn or broken cushion may lower the attenuation of the ear-muff. We recommend to replace the cushions as necessary, at least every 6 months in order to guarantee the best performance and hygiene.



1

The old ear cushions can be pulled away by hand. Cushions are recommended for disposal by following the principals of recycling PVC.



2

Next, pull out the insulation foam. Make sure that the cup is clean and dry.



3

Order the appropriate replacement parts in good time from your reseller. Hygiene kit includes two ear cushions and insulation foams for the earcups.



4

Flexible insulation foam is ideal for easy installation. Ensure the foam is completely inside and finish the surface with your fingers.



5

Hygiene kit includes two ear cushions. They are easy to pull out by hand.



6

Starting at the bottom, place the new ear cushions carefully. Press them on all areas into their proper place on the ear-cups.

STORAGE

Before and after using ear-muffs store them in a clean dust-free place. After long-term use it is recommended to turn the ear cups outwards to allow the insulation foam to dry.

SILENTA®

Silenta Group Oy • Länsiväylä 7 • 40700 Jyväskylä, Finland

Postal address: Silenta Group Oy • P.O. Box 10 • FI-40701 Jyväskylä, Finland

Telephone +358 14 3771522 • Fax +358 14 3771622
E-mail: silenta@silenta.com • www.silenta.com

